

Theory of Machines (HTM)



GEAR TOOTH FORM APPARATUS HTM7



Year 1 study

Features

- Bench or Wall mounted apparatus
- Two connecting gears supplied
- One gear for measuring
- Drawing of Involute Gear form
- Theory and terminology clearly labelled on unit

Description

A bench top base plate contains all elements for this experiment. Three gears are located onto the base plate. A large gear and small gear mesh together and can be rotated to produce analysis of ratios. A third gear is removable to allow students to review its tooth form, pitch circle diameter (PCD) and other key geometry of a tooth form. The apparatus also explains the form of an involute curve and how this is used to create a gear tooth profile. To help describe what an involute curve is, paper can be placed into the apparatus and an involute curve drawn. A set of vernier calipers is provided to allow the removable gear to be measured to help give a practical analysis of the gear form. Labels are used on the unit to help clearly explain gear theory.

Related Laws/Applications

- Spur Gears
- · Involute Gear Form and creation
- Meshing
- Gear Geometry
- Module
- Pitch Circle Diameter (PCD)
- Number of Teeth
- Ratios

Learning capabilities

- Experimental determination of shape and construction of an involute curve
- Explanation of Gear Form
- Explanation of Gear Ratios
- Explanation of Gear Modules
- Explanation of Gear Trains and Rotational Direction

sales@p-a-hilton.co.uk 01794 388 382

www.p-a-hilton.co.uk



Technical Specification

- Large (Mod 4) gears
- Large gear: 50 tooth, Module 4, 200mm PCD
- Small gear: 18 tooth, Module 4, 72mm PCD
- Removable gear module 12.5

What's in the Box?

- 1 x HTM7 Assembly
- 1 x Digital Vernier
- · Spare Cord
- 5 x Pencil
- · Instruction manual
- · Packing list
- Test sheet

You might also like

- HTM25
- HTM73
- HTM13
- HTM98

Weights & Dimensions

• Weight: 13 kg

· Length: 690mm

• Width: 530mm

• Height: 80mm

Essential Services

· Sturdy Bench top

Operational Conditions

- Storage temperature: -10°C to +70°C
- Operating temperature range: +10°C to +50°C
- Operating relative humidity range: 0 to 95%, non condensing

Ordering information

To order this product, please call PA Hilton quoting the following code: HTM7

All brand and/or product names are trademarks of their respective owners. Specifications and external appearance are subject to change without notice. The colour of the actual product may vary from the colour shown in the brochure.

Copyright © 2018 P.A. Hilton Limited. All rights reserved. This technical leaflet, its contents and/or layout may not be modified and/or adapted, copied in part or in whole and/or incorporated into other works without the prior written permission of P. A. Hilton Limited. Hi-Tech Education is a registered trade mark of P. A. Hilton Limited.